

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M30X60

Article number	01410.300.060
Brand	-
UBB	950351204017
UNSPSC	31161620
EAN	8715492410856
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NF	E25-114
ISO	4017
DIN	933
ASME	B18.2.3.1M
NEN	1568

Technical Specification

d-D	M30
k	18.7
L (mm)	60

Technical Drawing

P	3.5
s	46

