

## Hexagon head bolt oversized thread DIN 931 Steel Hot dip galvanized 8.8 M27X100

Article number	01420.270.100
Brand	-
UBB	950351209065
UNSPSC	31161620
EAN	8715492411945
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M27
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

#### Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

### Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931

b (min.): 125mm $L \leq 200$ mm	66
b (min.): $L > 200$ mm	79
b (min.): $L \leq 125$ mm	60
d-D	M27
k	17
L (mm)	100
P	3
s	41

