



**PEINER HV structural bolt  
EN 14399-4 Steel Plain 10.9  
M24X115**

|                |               |
|----------------|---------------|
| Article number | 04005.240.115 |
| Brand          | -             |
| UBB            | 500644669516  |
| UNSPSC         | 31161614      |
| EAN            | 8717077015845 |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                   |               |
|-------------------|---------------|
| Diameter          | M24           |
| Length            | 115 mm        |
| Class             | 10.9          |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement. PEINER  
HV-bolts and  
corresponding  
HV-nuts and HV-  
washers, sizes  
M12 up to M36  
are specified in EN  
14399-4 and EN  
14399-6. Diameters  
M39 up to M72  
are defined in  
DASSt directive  
021. PEINER HV-  
bolts with associated  
HV-nuts and HV-  
washers may be

**Standards**

|    |         |
|----|---------|
| EN | 14399-4 |
|----|---------|

**FABORY** used only as a set  
from one and the  
same supplier.

### Technical Specification

|        |     |
|--------|-----|
| b      | 39  |
| d-D    | M24 |
| k      | 15  |
| L (mm) | 115 |
| P      | 3   |
| s      | 41  |

### Technical Drawing

