

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M20X65

Article number	04101.200.065
Brand	-
UBB	500648306107
UNSPSC	31161620
EAN	8717077207509
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	65 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	65
P	2.5
s	30

Technical Drawing

