

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M20X100

Article number	04101.200.100
Brand	-
UBB	500648306776
UNSPSC	31161620
EAN	8717077207561
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-112
DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	100
P	2.5
s	30

Technical Drawing

