

## Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M20X70



Article number	04104.200.070
Brand	-
UBB	500614317278
UNSPSC	31161620
EAN	8715494454599
PKG. of 1	Full Box Only

### Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	70
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

### Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

### Technical Specification

b (min.): 125mm<L≤200mm	52
b (min.): L>200mm	65
b (min.): L≤125mm	46
k	12.5
P	2.50
s	30

### Technical Drawing

