

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M24X100

Article number	04104.240.100
Brand	-
UBB	500614317765
UNSPSC	31161620
EAN	8715494454643
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3

Technical Drawing



