

## Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M10X80



Article number	04105.100.080
Brand	-
UBB	500505561125
UNSPSC	31161620
EAN	8715494439152
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	80
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Wrench width (s) (mm)	17
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

### Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NF	E25-112

### Technical Specification

b (min.): 125mm < L ≤ 200mm	32
b (min.): L > 200mm	45
b (min.): L ≤ 125mm	26
k	6.4
P	1.50

### Technical Drawing



