

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X120

Article number	04105.120.120
Brand	-
UBB	500505562297
UNSPSC	31161620
EAN	8715494439367
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	120
P	1.75

Technical Drawing



