

## Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M16X70

|                |               |
|----------------|---------------|
| Article number | 04105.160.070 |
| Brand          | -             |
| UBB            | 500505563022  |
| UNSPSC         | 31161620      |
| EAN            | 8715494439503 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                   |                                                                              |
|-------------------|------------------------------------------------------------------------------|
| Diameter          | M16                                                                          |
| Length            | 70 mm                                                                        |
| Class             | 10.9                                                                         |
| Driving features  | Hexagon                                                                      |
| Head shape        | Hexagon head                                                                 |
| Material          | Steel                                                                        |
| Thread direction  | Right                                                                        |
| Surface treatment | Zinc flake Cr6+free -<br>ISO 10683 flZnnc                                    |
| Thread            | Metric thread                                                                |
| Info              | A zinc flake coating<br>eliminates the<br>risk of hydrogen<br>embrittlement. |

### Standards

|      |            |
|------|------------|
| ISO  | 4014       |
| NF   | E25-112    |
| DIN  | 931        |
| NEN  | 1555       |
| ASME | B18.2.3.1M |

### Technical Specification

|                           |     |
|---------------------------|-----|
| b (min.):<br>125mmL≤200mm | 44  |
| b (min.): L200mm          | 57  |
| b (min.): L≤125mm         | 38  |
| d-D                       | M16 |
| k                         | 10  |
| L (mm)                    | 70  |
| P                         | 2   |

### Technical Drawing



