

Hexagon head bolt DIN 931 Steel Plain 12.9 M10X80

Article number	04108.100.080
Brand	-
UBB	955351408674
UNSPSC	31161620
EAN	8715493849662
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	80 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1555
DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	80
P	1.5
s	17

Technical Drawing

