

Hexagon head bolt DIN 931 Steel Plain 12.9 M12X110

Article number	04108.120.110
Brand	-
UBB	955351409664
UNSPSC	31161620
EAN	8715493849761
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	110 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NEN	1555
ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	110
P	1.75
s	19

Technical Drawing

