

Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M24X1,50X110



Article number	04161.240.110
Brand	-
UBB	500644713736
UNSPSC	31161620
EAN	8717077019928
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	110 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	8765
NEN	1555
DIN	960
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	110
P	1.5

Technical Drawing



