



**PEINER HV structural bolt
EN 14399-4 Steel Hot dip
galvanized 10.9 M30X155**

Article number	04210.300.155
Brand	-
UBB	500644720251
UNSPSC	31161614
EAN	8717077020573
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	155 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info Full boxes only.European constructions must meet the requirements of the Construction Products Regulation 305/2011 in order to guarantee the safety of persons and objects.To this end, construction products according to harmonized European standards (hEN) are used.For preloaded joints, fasteners according to the standard series EN 14399 are

Standards

EN	14399-4
----	---------

available. Products according to EN 14399 may only be combined if they are from one and the same manufacturer, who has tested the sets and guarantees their functionality. The PEINER HV bolts, nuts and washers according to EN 14399-4 and EN 14399-6 are marked with "HV" (washers with "H" or "HV"). They are packed separately in sealed boxes and the packaging bears the CE mark. PEINER is CE certified for the production of these sets and a Declaration of Performance (DoP) is available. PEINER HV-bolts and corresponding HV-nuts and HV-washers, sizes M12 up to M36 are specified in EN 14399-4 and EN 14399-6. Diameters M39 up to M72 are defined in DAST directive 021. PEINER HV-bolts with associated HV-nuts and HV-washers may be used only as a set from one and the same supplier.

Technical Specification

b	44
d-D	M30
k	19
L (mm)	155

Technical Drawing

