



## Hexagon socket head cap screw DIN 912 Steel Plain 12.9 M22X90

|                |               |
|----------------|---------------|
| Article number | 07000.220.090 |
| Brand          | -             |
| UBB            | 952351345410  |
| UNSPSC         | 31161605      |
| EAN            | 8715492047472 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M22              |
| Length            | 90 mm            |
| Class             | 12.9             |
| Driving features  | Hexagon socket   |
| Head shape        | Cylindrical head |
| Material          | Steel            |
| Thread direction  | Right            |
| Surface treatment | Plain            |
| Thread            | Metric thread    |

#### Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Standards

|      |          |
|------|----------|
| NEN  | 1241     |
| ISO  | 4762     |
| BS   | 4168-1   |
| DIN  | 912      |
| ASME | B18.3.1M |
| NF   | E25-125  |

### Technical Specification

|                         |     |
|-------------------------|-----|
| b                       | 56  |
| d-D                     | M22 |
| dk (max.)               | 33  |
| Full thread if $L \leq$ | 70  |
| k (max.)                | 22  |
| L (mm)                  | 90  |
| P                       | 2.5 |
| s                       | 17  |

### Technical Drawing

