



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M33X70

Article number	07015.330.070
Brand	-
UBB	500644768102
UNSPSC	31161605
EAN	8717077025363
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M33
Length	70 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

BS	4168-1
DIN	912
NF	E25-125
NEN	1241
ASME	B18.3.1M
ISO	4762

Technical Specification

b	78
d-D	M33
dk (max.)	50
Full thread if $L \leq$	100
k (max.)	33
L (mm)	70
P	3.5
s	24

Technical Drawing

