



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M5X14

Article number	07023.050.014
Brand	-
UBB	500647936938
UNSPSC	31161605
EAN	8717077281714
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	14 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1241
NF	E25-125
ISO	4762
BS	4168-1
DIN	912
ASME	B18.3.1M

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if $L \leq$	25
k (max.)	5
L (mm)	14
P	0.8
s	4

Technical Drawing

