



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X270

Article number	07060.300.270
Brand	-
UBB	500644803172
UNSPSC	31161605
EAN	8717077028869
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	270 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1241
ISO	4762
ASME	B18.3.1M
NF	E25-125
DIN	912
BS	4168-1

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if $L \leq$	100
k (max.)	30
L (mm)	270
P	3.5
s	22

Technical Drawing

