



Hexagon socket head cap screw DIN 912 Steel Plain 8.8 M30X490

Article number	07060.300.490
Brand	-
UBB	500644805078
UNSPSC	31161605
EAN	8717077029057
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	490 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.3.1M
NF	E25-125
NEN	1241
ISO	4762
BS	4168-1
DIN	912

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if $L \leq$	100
k (max.)	30
L (mm)	490
P	3.5
s	22

Technical Drawing

