



Hexagon socket head cap screw fully threaded DIN ≈912 Steel Zinc plated 8.8 M16X70

Article number	07071.160.070
Brand	-
UBB	500500825079
UNSPSC	31161605
EAN	8715494042253
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	70 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	≈912
ASME	≈B18.3.1M
NF	≈E25-125
NEN	≈1241
ISO	≈4762
BS	≈4168-1

Technical Specification

d-D	M16
dk (max.)	24
k (max.)	16
L (mm)	70
P	2
s	14

Technical Drawing

