



## Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M4X12

Article number	07141.040.012
Brand	-
UBB	951351888114
UNSPSC	31161518
EAN	8715492067616
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M4
Length	12 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

#### Info

Warning: electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

### Standards

ISO	7380-2
-----	--------

**FABORY** with a '0' preceding  
the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M4
dc (max.)	9.4
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	12
P	0.7
s	2.5

## Technical Drawing

