



**Hexagon socket button head screw with flange ISO 7380-2
Steel Zinc plated 010.9 M5X8**

Article number	07141.050.008
Brand	-
UBB	951351888601
UNSPSC	31161518
EAN	8715492067692
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning:
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

ISO	7380-2
-----	--------

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

d-D	M5
dc (max.)	11.8
Full thread if $L \leq$	25
k (max.)	2.75
L (mm)	8
P	0.8
s	3

Technical Drawing

