



**Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M5X30**

|                |               |
|----------------|---------------|
| Article number | 07150.050.030 |
| Brand          | -             |
| UBB            | 950351438177  |
| UNSPSC         | 31161518      |
| EAN            | 8715492068798 |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                   |                |
|-------------------|----------------|
| Diameter          | M5             |
| Length            | 30 mm          |
| Class             | 010.9          |
| Driving features  | Hexagon socket |
| Head shape        | Button head    |
| Material          | Steel          |
| Thread direction  | Right          |
| Surface treatment | Plain          |
| Thread            | Metric thread  |

Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

**Standards**

|      |           |
|------|-----------|
| ISO  | 7380-1    |
| NF   | ≈E25-126  |
| BS   | ≈4168-6   |
| ASME | ≈B18.3.4M |

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

|                         |      |
|-------------------------|------|
| d-D                     | M5   |
| dk (max.)               | 9.5  |
| Full thread if $L \leq$ | 25   |
| k (max.)                | 2.75 |
| L (mm)                  | 30   |
| P                       | 0.8  |
| s                       | 3    |

## Technical Drawing

