



**Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M5X35**

Article number	07150.050.035
Brand	-
UBB	950351946120
UNSPSC	31161518
EAN	8715492068804
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	M5
Length	35 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

**Standards**

ISO	7380-1
BS	≈4168-6
ASME	≈B18.3.4M
NF	≈E25-126

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M5
dk (max.)	9.5
Full thread if $L \leq$	25
k (max.)	2.75
L (mm)	35
P	0.8
s	3

## Technical Drawing

