



Hexagon socket button head
screw ISO 7380-1 Steel Plain
010.9 M6X16

Article number	07150.060.016
Brand	-
UBB	950351438664
UNSPSC	31161518
EAN	8715492068910
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. Due
to the unfavourable
head geometry
these fasteners
have reduced
loadability. Steel
fasteners with
reduced loadability
are marked with a
'0' preceding the
property class mark,
e.g. '010.9'. Stainless
steel fasteners with
reduced loadability
are either marked
with a '0' preceding

Standards

ASME	≈B18.3.4M
BS	≈4168-6
NF	≈E25-126
ISO	7380-1

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

d-D	M6
dk (max.)	10.5
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	16
P	1
s	4

Technical Drawing

