



## Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M8X25

Article number	07150.080.025
Brand	-
UBB	950351439654
UNSPSC	31161518
EAN	8715492069092
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M8
Length	25 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

#### Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

### Standards

BS	≈4168-6
ISO	7380-1
ASME	≈B18.3.4M
NF	≈E25-126

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M8
dk (max.)	14
Full thread if $L \leq$	35
k (max.)	4.4
L (mm)	25
P	1.25
s	5

## Technical Drawing

