



Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M10X55

Article number	07150.100.055
Brand	-
UBB	950351948936
UNSPSC	31161518
EAN	8715492069320
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	55 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

NF	≈E25-126
BS	≈4168-6
ISO	7380-1
ASME	≈B18.3.4M

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M10
dk (max.)	17.5
Full thread if $L \leq$	40
k (max.)	5.5
L (mm)	55
P	1.5
s	6

## Technical Drawing

