



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M10X155

Article number	07160.100.155
Brand	-
UBB	500645101055
UNSPSC	31161605
EAN	8717077059986
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	155 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
ISO	4762
BS	4168-1
NF	E25-125
DIN	912
NEN	1241

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	155
P	1.5
s	8

Technical Drawing

