

Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M10X170



| | |
|----------------|---------------|
| Article number | 07160.100.170 |
| Brand | - |
| UBB | 500645101139 |
| UNSPSC | 31161605 |
| EAN | 8717077059993 |
| PKG. of 50 | Full Box Only |

Technical Parameters

| | |
|-----------------|-----|
| Diameter (d-D) | M10 |
| Length (L) (mm) | 170 |
| Class | 8.8 |

Standards

| | |
|------|----------|
| ISO | 4762 |
| DIN | 912 |
| ASME | B18.3.1M |
| NF | E25-125 |
| BS | 4168-1 |

Technical Specification

| | |
|-------------------------|------|
| b | 32 |
| d_k (max.) | 16 |
| Full thread if $L \leq$ | 40 |
| k (max.) | 10 |
| P | 1.50 |
| s | 8 |

Technical Drawing

