



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M10X220

Article number	07160.100.220
Brand	-
UBB	500645101477
UNSPSC	31161605
EAN	8717077060029
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	220 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4762
NEN	1241
NF	E25-125
ASME	B18.3.1M
BS	4168-1
DIN	912

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	220
P	1.5
s	8

Technical Drawing

