



Hexagon socket countersunk head screw ISO 10642 Steel Plain 010.9 M20X55

Article number	07400.200.055
Brand	-
UBB	951351670702
UNSPSC	31161518
EAN	8715492084354
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	55 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. All
thread lengths
are guide values
only and may
deviate. Due to
the unfavourable
head geometry
these fasteners
have reduced
loadability. Steel
fasteners with
reduced loadability
are marked with a
'0' preceding the
property class mark,

Standards

DIN	≈7991
ISO	10642

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	60
d-D	M20
dk (max.)	36.75
Full thread if $L \leq$	90
k (max.)	10.16
L (mm)	55
P	2.5
s	12
α	90

Technical Drawing

