



## Hexagon socket countersunk head screw ISO 10642 Steel Zinc plated 8.8 M4X50

Article number	07470.040.050
Brand	-
UBB	950351953878
UNSPSC	31161518
EAN	8715492151193
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M4
Length	50 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

#### Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

### Standards

DIN	≈7991
ISO	10642

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	20
d-D	M4
dk (max.)	7.96
Full thread if $L \leq$	25
k (max.)	2.48
L (mm)	50
P	0.7
s	2.5
$\alpha$	90

## Technical Drawing

