

Hexagon nut ISO 4032 Steel Plain 5-2 for pressure vessels M36

Article number	08781.360.001
Brand	-
UBB	500579966002
UNSPSC	31161727
EAN	8715494421102
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Class	5-2
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property

Standards

ISO	4032
-----	------

FABORY

class and the
manufacturer's mark.
This recognition is
equally accepted
by Lloyd's Register
Energy for pressure
vessels

Technical Specification

d-D	M36
m (max.)	31
P	4
s	55

Technical Drawing

