



Hexagon slotted and castle nut DIN 935-1 Steel Plain 4 M18

Article number	12000.180.001
Brand	-
UBB	950355104379
UNSPSC	31161707
EAN	8715492575388
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M18
Class	4
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Up to and including M12 slotted and castle nuts are class 5, above size M12 class 4. Up to and including M39 slotted and castle nuts are provided with 6 slots, above M39 with 8 slots.* These dimensions are supplied with the 'old' widths across flats sizes according to DIN. Guide values for advised split pins (cotter pins) acc. to DIN 94 (ISO 1234). Depending on availability the

Standards

DIN	935-1
NEN	729

dimensions may
deviate.

FABORY

Technical Specification

d-D	M18
m	21
n	4.5
Number of slots	6
P	2.5
s	27
Split pin DIN 94	4

Technical Drawing

