



Slotted screw insert type A DIN 7965 Steel Plain M12X25

Article number	14410.120.025
Brand	-
UBB	500645173161
UNSPSC	31161727
EAN	8717077067943
PKG. of 100	Full Box Only

Technical Parameters

Length	25 mm
Driving features	Slotted
Material	Steel
Surface treatment	Plain
Thread	Metric thread
Type no.	A
Info	It is recommended that the exact pilot hole diameter selection is made on basis of tests.

Standards

DIN	7965
-----	------

Technical Specification

d-D	M12
d2	22
L (mm)	25
n	3
P	1.75
Pilot hole ø	19

Technical Drawing

