

Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 5/8X45 (1.3/4)



Article number 22080.158.044

Brand -

UBB 500578015868

UNSPSC 31161619

EAN 8715494337625

PKG. of 1 Full Box Only

Technical Parameters

Diameter (inch) 5/8

Length (L) (mm) 45

Length (L) (Inch - ft) 1.3/4

Info Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Class Gr.B7 - Gr.2H

Material Steel

Material technical ASTM A193 - ASTM A194

Thread direction Right

Surface treatment Plain

Thread Unified National Coarse

Standards

ASTM A193/A194

BS ≈4882

ASME B16.5/B18.2.2

Technical Specification

B 1.1/16

Technical Drawing

M	15.5
Threads per inch	11

