



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193
- ASTM A194 Plain Gr.B7 -
Gr.2H 5/8X265 (10.1/2)**

Article number	22080.158.266
Brand	-
UBB	500578016932
UNSPSC	31161619
EAN	8715494337731
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	265 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Technical Specification

B	1.0625
---	--------

Technical Drawing

L (mm)	265
M	15.5

