



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Steel ASTM A193  
- ASTM A194 Plain Gr.B7 -  
Gr.2H 3/4X95 (3.3/4)**

Article number	22080.191.095
Brand	-
UBB	950353064716
UNSPSC	31161619
EAN	8715492617446
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	3/4 Inch
Length	95 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	10

Info  
Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

**Technical Specification**

B	1.25
---	------

**Technical Drawing**

L (mm)	95
M	18.7

