

Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 3/4X110 (4.1/4)



Article number	22080.191.107
Brand	-
UBB	950353064971
UNSPSC	31161619
EAN	8715492617460
PKG. of 1	Full Box Only

Technical Parameters

Diameter (inch)	3/4
Length (L) (mm)	110
Length (L) (Inch - ft)	4.1/4

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

Technical Specification

B	1.1/4
---	-------

Technical Drawing

M	18.7
Threads per inch	10

