



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193
- ASTM A194 Plain Gr.B7 -
Gr.2H 3/4X235 (9.1/4)**

Article number	22080.191.234
Brand	-
UBB	500578019589
UNSPSC	31161619
EAN	8715494337991
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	235 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	10

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

Technical Specification

B	1.25
---	------

Technical Drawing

L (mm)	235
M	18.7

