



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 1 Inch X155 (6.1/8)

|                |               |
|----------------|---------------|
| Article number | 22080.254.155 |
| Brand          | -             |
| UBB            | 500578028655  |
| UNSPSC         | 31161619      |
| EAN            | 8715494343879 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                    |                         |
|--------------------|-------------------------|
| Diameter           | 1 Inch                  |
| Length             | 155 mm                  |
| Class              | Gr.B7 - Gr.2H           |
| Material           | Steel                   |
| Material technical | ASTM A193 - ASTM A194   |
| Thread direction   | Right                   |
| Surface treatment  | Plain                   |
| Thread             | Unified National Coarse |
| Threads per inch   | 8                       |

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

|      |               |
|------|---------------|
| BS   | ≈4882         |
| ASME | B16.5/B18.2.2 |
| ASTM | A193/A194     |

### Technical Specification

|   |       |
|---|-------|
| B | 1.625 |
|---|-------|

### Technical Drawing

L (mm) 155

M 25

