



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 3/8X60 (2.3/8)

Article number	22082.096.060
Brand	-
UBB	500578449331
UNSPSC	31161619
EAN	8715494369909
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	3/8 Inch
Length	60 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	16

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

### Technical Specification

B	0.6875
---	--------

### Technical Drawing

L (mm) 60

M 9

