



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Steel ASTM A193  
- ASTM A194 Zinc plated  
Gr.B7 - Gr.2H 5/8X75 (3)**

Article number	22082.158.076
Brand	-
UBB	951353663598
UNSPSC	31161619
EAN	8715493205499
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	5/8 Inch
Length	75 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

**Standards**

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

**Technical Specification**

B	1.0625
---	--------

**Technical Drawing**

L (mm) 75

M 15.5

