



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193
- ASTM A194 Zinc plated
Gr.B7 - Gr.2H 5/8X85 (3.3/8)**

| | |
|----------------|---------------|
| Article number | 22082.158.085 |
| Brand | - |
| UBB | 500578453697 |
| UNSPSC | 31161619 |
| EAN | 8715494375306 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|-------------------------|
| Diameter | 5/8 Inch |
| Length | 85 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Unified National Coarse |
| Threads per inch | 11 |

| | |
|------|---|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|---|

Standards

| | |
|------|---------------|
| ASME | B16.5/B18.2.2 |
| BS | ≈4882 |
| ASTM | A193/A194 |

Technical Specification

| | |
|---|--------|
| B | 1.0625 |
|---|--------|

Technical Drawing

| | |
|--------|------|
| L (mm) | 85 |
| M | 15.5 |

