



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 1.7/8X480 (18.7/8)

Article number	22090.476.480
Brand	-
UBB	500578512500
UNSPSC	31161619
EAN	8715494384513
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.7/8 Inch
Length	480 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	2.9375
L (mm)	480

Technical Drawing

