



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Steel ASTM A193  
- ASTM A194 Zinc plated  
Gr.B7 - Gr.2H 1.1/8X510 (20)**

|                |               |
|----------------|---------------|
| Article number | 22092.285.508 |
| Brand          | -             |
| UBB            | 500578080607  |
| UNSPSC         | 31161619      |
| EAN            | 8715494317061 |
| PKG. of 1      | Full Box Only |

**Technical Parameters**

|                    |                       |
|--------------------|-----------------------|
| Diameter           | 1.1/8 Inch            |
| Length             | 510 mm                |
| Class              | Gr.B7 - Gr.2H         |
| Material           | Steel                 |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction   | Right                 |
| Surface treatment  | Zinc plated           |
| Thread             | 8 Unified National    |
| Threads per inch   | 8                     |

|      |                                                                                                                                                                                                                  |
|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

**Standards**

|      |               |
|------|---------------|
| ASME | B16.5/B18.2.2 |
| ASTM | A193/A194     |
| BS   | ≈4882         |

**Technical Specification**

|        |        |
|--------|--------|
| B      | 1.8125 |
| L (mm) | 510    |

**Technical Drawing**

