



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 1.1/4X390 (15.3/8)

Article number	22092.317.390
Brand	-
UBB	500578086315
UNSPSC	31161619
EAN	8715494317634
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/4 Inch
Length	390 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National
Threads per inch	8

Info Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

B	2
L (mm)	390
M	31

