



**Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 1.3/4X460 (18.1/8)**

Article number	22092.444.460
Brand	-
UBB	500578113614
UNSPSC	31161619
EAN	8715494312073
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	1.3/4 Inch
Length	460 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National
Threads per inch	8

Info      Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

B	2.75
L (mm)	460
M	43.6

