



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 2 Inch X385 (15.1/4)

Article number	22092.508.387
Brand	-
UBB	500578121799
UNSPSC	31161619
EAN	8715494317856
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2 Inch
Length	385 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National
Threads per inch	8

Info
Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

B	3.125
L (mm)	385
M	50

