



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 2 Inch X425 (16.3/4)

| | |
|----------------|---------------|
| Article number | 22092.508.425 |
| Brand | - |
| UBB | 500578122458 |
| UNSPSC | 31161619 |
| EAN | 8715494317924 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|-----------------------|
| Diameter | 2 Inch |
| Length | 425 mm |
| Class | Gr.B7 - Gr.2H |
| Material | Steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | 8 Unified National |
| Threads per inch | 8 |

Info Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

| | |
|------|---------------|
| ASME | B16.5/B18.2.2 |
| ASTM | A193/A194 |
| BS | ≈4882 |

| | |
|--------|-------|
| B | 3.125 |
| L (mm) | 425 |
| M | 50 |

